
Prism Nano



- 33 Lumens/Module
- 150 modules per 60 watt PS
 - Max 50 modules per run, 3 runs per 60 watt power supply
- Each bag has 150 modules
- Each carton has 7 bags
- 3000K,4000K,5000K,6500K and 7200K






Prism Nano

Target Application – 30mm (1.2" block acrylic letters)


- Mount the LED facing towards the back
- 50mm (2") max width for single row
- 45mm (1.77") spacing for multiple rows



Page 4

© SloanLED 2018






Block out film, 25-30mm wide.

Make sure the glue layer is also
white for optimum light
reflection and even output on
the face.


















How to sell Prism Nano

- Identify the application
- Samples/Samples get the customer to test in block acrylic letters
- Discuss other kelvin options

